
## NESSessities



## **NESS** Pump vent

## Venting pumps safely and without tools

Thermal oil pumps must be vented during commissioning and on each start up of a plant in order to avoid dry running.

Dry running of the pump would, among other things, damage the mechanical seal and therefore results in a standstill of the pump and the system or even leads to oil leakage and a fire.

Venting the pump usually requires tools, but the work is also not entirely safe for the operating personnel.

For this reason, we have developed a 350°C-resistant pump vent with a needle valve for simple and safe venting.

Suitable for retrofitting KSB, Allweiler, Speck, Sterling and Dickow pumps, among others with 1/4" thread.

## Ihre Vorteile im Überblick

- Temperature resistant venting
- Easy assembly
- Easy operation
- Manufacturer-independent
  retrofittable





